



Shop Order

Customer: Stock

Dealer: AEV

Exp. Date: 12/28/2022  
 Quote No: 10359-0001  
 11/28/2022 16:12:54

Job/Order No: 24DF30631-30640G

Page 1

PART NO	S	DESCRIPTION	QTY
00-00-0010		-- ORDER NUMBER	1
00-00-0107		-- Order Date: Post August 1st, 2022	1
00-00-0113		-- Ambulance Built to Star Of Life KKK-A-1882-F Certification, Latest Revision	1
00-10-0015		Vehicle Quantity (Vehicles)	1
00-91-0003		CHASSIS VIN NUMBER:	1
00-91-0009		ACCOUNT SPECIALIST: **MUST CHOOSE AN ACCOUNT SPECIALIST**	1
00-91-0027		REFERENCE UNIT #:	1
00-91-0028		RE-WRITE DATE :	1
00-91-0040		SEAT BELT POSITIONS MODS	1
00-91-0042		-- CAB SEAT BELT MOD:	1
00-91-0044		-- Total: 2 Seated Positions in Chassis Cab	1
00-91-0050		-- REAR SEAT BELT MOD:	1
00-91-0053		-- Total: FILL IN NUMBER OF POSITIONS	1
00-99-9000		Revision Level: 0 - Zero - ORIGINAL VERSION	1
00-99-9030		Change Order Level: 0 - Zero - ORIGINAL VERSION	1
01-3F-0000		Type III AEV Traumahawk Cut-A-Way, Modular Ambulance	1
01-AT-3F44		2024 Ford, E-450 DRW Cut-away, 158", Hi Trim, Gas Spec to be updated when received from Ford. 2024 Ford E-450 E4F Cutaway Chassis 158" Wheelbase GVWR 14,500 pounds 7.3L V8 Gasoline Engine 350 HP premium Exterior Oxford White	1
01-FM-EWH1		-- Wheel Simulators: Phoenix, Polished Stainless steel, E-Series	1
01-FM-TI08		-- Tire, SPARE: All season, Random Make LT225/75 R16, LR E	1
01-FM-TI01		-- Location: Shipped Loose	1
01-TU-0100		-- Jack and Tire Tools: None	1
01-OE-47C0		-- Throttle Control System	1
03-EA-43PR		-- Side Mirrors, OEM Black Telescope -E Series	1
ZZ-ZZ-ZZZZ			1
00-99-0180		Chassis Axle Digital Alignment	1

PART NO	S	DESCRIPTION	QTY
01-Y0-0002		BODY Generation 10	1
01-X0-0002		-- Body Certification Provided to Specification -Gen 10 The Body Manufacturing group certifies that this Ambulance Modular body has been constructed of materials and methods that meet or exceed the standards as required by the AEV Generation 10 Body Specification of February 24, 2022 as published. The body shall be built and constructed to the submitted work order and the AEV Generation 10 build standards without exception. Any Deviations to the work order or Generation 10 build standards must have written authorization prior to body delivery to AEV by the AEV Body Engineer on file.	1
02-00-0002		-- Body Build Information Body Number; Account Manager; Chassis Type : Mickey Body Due Date;	1
02-00-0003		-- ALL DIMENSIONS ON ORDER WILL HAVE A VARIABLE OF + OR - 1/4" Unless specified as a minimum dimension.	1
02-B2-3F72		<b>Body, Module: Cut-away, 172 x 95 x 72" Interior Head Room</b>	1
02-00-0006		-- Headroom: 74/72" Finished Interior - Ducted A/C	1
02-00-0060		-- Compartment and Entry door Full length Stainless Steel Hinges std	1
02-B0-3F2E		-- Cab Extension: 10-inch - allows full OEM seat travel + 4"	1
02-B0-CC01		-- Compartment Construction: STANDARD, Unless Specified Otherwise Sides and Back: .100 Polished Aluminum Diamond Plate Compartment Ceiling: .090 Aluminum Sheet	1
02-B0-SFL0		-- Compt Floors: Sweep-out, even with bottom door jamb Unless Specified Otherwise.	1
02-B0-CC41		-- Compartment floor thickness .125" standard	1
02-B0-CC18		-- Compartment Ventilation - Flap style #VT-2495-A01, STD	1
02-B0-CE03		-- Curb side Entry Door (CSE): 73.8 High x 31 Wide - 164+	1
02-B0-09B2		-- C/S Door Check : Double Action Gas Shock	1
04-EA-09B1		-- Door Swing Angle: Set to 90-100 degrees	1
02-B0-CESL		-- Curbside Entry Door (CSE) Location: Standard, Rearward of M-7 Compt if Optioned	1
ZZ-ZZ-ZZZZ		--	1
02-B1-SW64		-- Step Well, CURBSIDE Entry Door, 1-Step Diamond Plate	1
05-IL-09SW		-- Light, Step Well: 3" Weldon, White, Activate with C/S entry door Light shall come on with CS door or with right flood switch.	1
02-B1-M163		-- M-1 Compt (LF): 72 HR, 79.8" H x 18.6" W x 19.4" D	1
02-B0-CC02		-- Compartment Construction: STANDARD Diamond Plate Sides and Back: .100 Polished Aluminum Diamond Plate Compartment Ceiling: .090 Aluminum Sheet	1
02-B0-CC08		-- Compartment Door Panel: Diamond Plate	1
12-DC-GA10		-- Compartment Finish: Diamond Plate Standard	1
02-B0-CC16		-- Compartment Door Ventilation - small punched half-moon Louvered Door	1
02-B0-SWFL		-- Compt Floor: Sweep-out, even with bottom door jamb.	1
02-B0-CC41		-- Compartment floor thickness .125" standard	1
02-BC-10A5		-- Compartment Door: SINGLE DOOR, Forward hinged 2-point Latch	1
02-B0-09B0		-- Compt Door Check: Double Action Gas Shock	1
04-EA-09B1		-- Door Swing Angle: Set to 90-100 degrees	1
05-EL-40N1		-- Light, Compt, LED, M-1 (LF): Intertek Model No ZY-156-LEDC, MTB 1" Hole, Centered	1

PART NO	S	DESCRIPTION	QTY
08-B1-02LI		<i>/-- Prep for 02 Lift: NONE</i>	1
12-ZZ-ZZZZ		<i>/--</i>	1
02-B1-M264		<i>/-- M-2 Compt (LFM): 31.5" H x 44.5" W x 19.4" D</i>	1
02-B0-CC02		<i>/-- Compartment Construction: STANDARD Diamond Plate</i> Sides and Back: .100 Polished Aluminum Diamond Plate Compartment Ceiling: .090 Aluminum Sheet	1
02-B0-CC08		<i>/-- Compartment Door Panel: Diamond Plate</i>	1
12-DC-GA10		<i>/-- Compartment Finish: Diamond Plate Standard</i>	1
02-B0-SWFL		<i>/-- Compt Floor: Sweep-out, even with bottom door jamb.</i>	1
02-B0-CC41		<i>/-- Compartment floor thickness .125" standard</i>	1
02-B1-BIO1		<i>/-- Bio-Waste: Diamond Plate Closeout for Bio in A/A</i> Dogleg for interior access bio-waste. 17" W x 13"H and compartment depth less 2".	1
02-BC-10D0		<i>/-- Doors, Compartment, DOUBLE DOORS (std)</i>	1
02-B0-09B0		<i>/-- Compt Door Check: Double Action Gas Shock</i>	1
04-EA-09B1		<i>/-- Door Swing Angle: Set to 90-100 degrees</i>	1
04-TS-11D3		<i>/-- M-2 Shelf, Adjustable, Ext: .125 Smooth Alum, 2" Upward lip</i>	1
04-TS-4010		<i>/-- Shelf Bracket: 90 Deg with Slotted Holes</i>	1
05-EL-40N2		<i>/-- Light, Compt, LED, M-2 (LFM): Intertek Model No ZY-156-LEDC, STD</i> MTB Note: 1" Hole, Centered in Compartment ceiling	1
05-HA-13HA		<i>/-- Condenser: OEM Only, Compt Floor Standard</i>	1
06-RR-13Z0		<i>/-- Standard Conduit: 1-1/2"', with pull wire</i>	1
06-RR-13O4		<i>/-- CONDUIT ORIGINATION POINT: M-2 compartment</i>	1
06-RR-13T3		<i>/-- CONDUIT TERMINATION POINT: Behind A/A Board (Panel)</i>	1
09-ZZ-ZZZZ		<i>/--</i>	1
09-ZZ-ZZZZ		<i>/--</i>	1
02-B5-M368		<i>/-- M-3 Compt (LR): 58.5" H x 33.1" W x 19.4 D</i> WITH 58.5" HIGH M3, THIS WILL NARROW THE TELEMETRY AREA & LP WILL PROBABLY NOT FIT	1
02-B0-CC02		<i>/-- Compartment Construction: STANDARD Diamond Plate</i> Sides and Back: .100 Polished Aluminum Diamond Plate Compartment Ceiling: .090 Aluminum Sheet	1
02-B0-CC08		<i>/-- Compartment Door Panel: Diamond Plate</i>	1
12-DC-GA10		<i>/-- Compartment Finish: Diamond Plate Standard</i>	1
02-B0-CC12		<i>/-- Compartment Ventilation - Compartment Ceiling O O O O</i> MTB NOTE: hat channel with three (4") holes above the hat at the ceiling level.	1
02-B0-SWFL		<i>/-- Compt Floor: Sweep-out, even with bottom door jamb.</i>	1
02-B0-CC41		<i>/-- Compartment floor thickness .125" standard</i>	1
02-BC-10A5		<i>/-- Compartment Door: SINGLE DOOR, Forward hinged 2-point Latch</i>	1
02-B0-09B0		<i>/-- Compt Door Check: Double Action Gas Shock</i>	1
04-EA-09B1		<i>/-- Door Swing Angle: Set to 90-100 degrees</i>	1
04-TS-11B0		<i>/-- Shelf, Adjustable, Ext: .125 smooth Aluminum, 2" Upward Lips</i>	1
04-TS-4010		<i>/-- Shelf Bracket: 90 Deg with Slotted Holes</i>	1
05-EL-40N3		<i>/-- Light, Compt, LED, M-3 (LR): Intertek Model No ZY-156-LEDC, STD</i> MTB Note: 1" Hole, Centered in Compartment ceiling	1

PART NO	S	DESCRIPTION	QTY
09-ZZ-ZZZZ		/--	1
02-B1-M571		/-- M-5 Compt (RR): 72 HR, 79.8" H x 25.5" W x 21"D	1
02-B0-CC02		/-- <b>Compartment Construction: STANDARD Diamond Plate</b> Sides and Back: .100 Polished Aluminum Diamond Plate Compartment Ceiling: .090 Aluminum Sheet	1
02-B0-CC08		/-- <b>Compartment Door Panel: Diamond Plate</b>	1
12-DC-GA10		/-- <b>Compartment Finish: Diamond Plate Standard</b>	1
02-B0-CC12		/-- <b>Compartment Ventilation - Compartment Ceiling O O O O</b> MTB NOTE: hat channel with three (4") holes above the hat at the ceiling level.	1
02-B0-CC16		/-- <b>Compartment Door Ventilation - small punched half-moon Louvered Door</b>	1
02-B0-SWFL		/-- <b>Compt Floor: Sweep-out, even with bottom door jamb.</b>	1
02-B0-CC41		/-- <b>Compartment floor thickness .125" standard</b>	1
02-BC-10A5		/-- <b>Compartment Door: SINGLE DOOR, Forward hinged 2-point Latch</b>	1
02-B0-09B0		/-- <b>Compt Door Check: Double Action Gas Shock</b>	1
04-EA-09B1		/-- <b>Door Swing Angle: Set to 90-100 degrees</b>	1
04-TS-17M5		/-- <b>M-5 Dividers, Adj: (1) 14x60 H, (1) 14x30 H, Opt #2</b>	1
04-TS-1001		/-- <b>Divider Material: .125 Smooth Aluminum Sheet</b>	1
04-TS-STR1		/-- <b>Strap: 2" Webb Seatbelt buckle chrome footman loops -Custom Length</b> ILOS	1
04-TS-STR2		/-- <b>2" Footman Loops: Locate back from jamb</b>	1
05-EL-40M5		/-- <b>Light, Compt, M-5 (RR): 4" Flush, T/L No 40003</b> MTB Note : 4 1/2" Light hole required, when Full Height compartment	1
09-ZZ-ZZZZ		/--	1
02-B1-M664		/-- M-6 Compt (RRFwd): 17.2" H x 13.5" W x 19.4" D	1
02-B0-CC02		/-- <b>Compartment Construction: STANDARD Diamond Plate</b> Sides and Back: .100 Polished Aluminum Diamond Plate Compartment Ceiling: .090 Aluminum Sheet	1
02-B0-CC08		/-- <b>Compartment Door Panel: Diamond Plate</b>	1
12-DC-GA10		/-- <b>Compartment Finish: Diamond Plate Standard</b>	1
02-B0-SWFL		/-- <b>Compt Floor: Sweep-out, even with bottom door jamb.</b>	1
02-B0-CC41		/-- <b>Compartment floor thickness .125" standard</b>	1
02-BC-10A3		/-- <b>Compartment Door: SINGLE DOOR, 1-point Latch Less than 15" wide</b>	1
02-B0-0012		/-- <b>Exterior Compartment Door Stop, Rubber Bumper, No Door Check</b> MTB; No Gas Strut Door check, Door is too narrow, less than 15", Rubber Door stop to be installed on exterior.	1
05-EL-40N6		/-- <b>Light, Compt, LED, M-6 (RRF): Intertek Model No ZY-156-LEDC, STD</b> MTB Note: 1" Hole, Centered in Compartment ceiling	1
09-ZZ-ZZZZ		/--	1
02-B1-M763		/-- M-7 Compt (RF): 72 HR, 46.6" H x 25.25" W, I/O to ALS	1
02-BC-10A0		/-- <b>Compartment Door: SINGLE DOOR, 1-point Latch</b>	1
02-B0-09B0		/-- <b>Compt Door Check: Double Action Gas Shock</b>	1
04-EA-09B1		/-- <b>Door Swing Angle: Set to 90-100 degrees</b>	1
05-EL-40M7		/-- <b>Light, Compt, M-7 (RF): NONE</b>	1
12-ZZ-ZZZZ		/--	1
02-B1-M864		/-- M-8 Drawer (RF): Batt, 164, 12.1" H x 25.25" W x 21" D	1
02-B0-CC00		/-- <b>Battery Drawer compartment Construction: STANDARD Diamond Plate</b> Sides and Back: .100 Polished Aluminum Diamond Plate Compartment Bottom: .125 Aluminum Sheet Compartment Ceiling: .090 Aluminum Sheet	1

PART NO	S	DESCRIPTION	QTY
02-B0-CC09		-- <b>Compartment Door Panel: Smooth Aluminum</b>	1
12-DC-GA10		-- <b>Compartment Finish: Diamond Plate Standard</b>	1
02-BC-10E0		-- <b>Drawer Front: 2-point latch</b>	1
05-ZZ-ZZZZ		--	1
02-B1-RA02		-- <b>Rear Access Doors: 46 3/4" Wide x 60 5/8" High</b>	1
ZZ-ZZ-ZZZZ		--	1
<b>WELDING - CELL 1</b>			
04-AS-06A0		Fuel Fill: CPI FG5301-1-238-U Open Housing, Polished Bezel - 53 degree (Std)	1
04-BW-AB95		-- Bumper, Rear: HD Alum Framed w/DP pontoon covers	1
04-BW-FLIM		-- Step, Center: 2" x 7" Grip strut, flip-up PURCHASED WITH BODY	1
04-BW-AF19		-- Fenders, Rear: Polished Aluminum	1
04-BW-DP01		-- Skirt Rails: Polished Aluminum Diamond Plate, Box style std	1
04-BW-DP02		-- Corner Caps: 17.3" High, Alum Diamond Plate If there is a body drop, add the appropriate height to Corner Caps.	1
ZZ-ZZ-ZZZZ		--	1
04-BW-DP03		-- Front Stone Guards: 17.3" High, Alum Diamond Plate If there is a body drop, add the appropriate height to Stone Guards.	1
04-BW-DP14		-- Rear Kick Plate: Polished Aluminum Diamond Plate	1
04-BW-TA03		-- Recessed Tag Area: Polished Aluminum Diamond Plate	1
04-BW-TA04		-- Location: Centered in the kick plate	1
05-EL-44TN		-- Tag Light: Kinequip LED #132703C	1
04-EA-1122		-- Mud Flaps Front: Modular, Rubber with AEV/Rev Logo std	1
04-EA-1132		-- Mud Flaps Rear: Modular, Rubber AEV LOGO	1
04-EA-09A0		(2) Rear Door Hold Opens: Grabber Style, 1 on each door	1
<b>EXTERIOR LIGHTING / HEAT/AC / INSULATION - CELL 2</b>			
05-EL-1800		CORNER CAP LED ICC/WARNING LIGHTS	1
05-EL-18F0		-- Front Corner Cap LED ICC/Warning Lights: Warnings RED/WHITE	1
05-EL-18F1		-- Front Center ICC Lts: (3) AMBER Kinequip LED No 112401A, Switch w/ Headlights.	1
ZZ-ZZ-ZZZZ		--	1
05-EL-18R5		-- Rear Corner Cap LED ICC/Warning Lights: Warnings RED/AMBER	1
05-EL-18R1		-- Rear Center ICC Lts: (3) RED Kinequip LED No 112401R Switch w/ Headlights	1
ZZ-ZZ-ZZZZ		--	1
06-SW-CC01		-- ICC Warning Lights Switched: Primary Only	1
ZZ-ZZ-ZZZZ		--	1
05-EL-42S0		<b>Tail Lights: TBD When Truck is Sold</b>	1
05-EL-44MK		-- <b>Side Marker Lts: (2) Trucklite #18300R Red</b>	1
05-ZZ-ZZZZ		--	1
05-EL-4315		Third Brake light, With Back-up Camera combo, see option 06-EC-3013	1
05-ZZ-ZZZZ		--	1
05-EL-4580		<b>SCENE/FLOOD LIGHTS (Whelen 900 LED-24 Series)</b>	1
05-EL-45L6		-- <b>Left Scene Lights: (2) LED-24, Whelen 900</b> Chrome flanges for this light included	1
06-EL-18LF		-- <b>Left Flood Activate: Left Flood Switch</b>	1
05-EL-45T6		-- <b>Right Scene Lights: (2) LED-24, Whelen 900</b> Chrome flanges for this light included	1
06-EL-18RT		-- <b>Right Flood Activate: Right Flood Switch and open CSE Door</b>	1

PART NO	S	DESCRIPTION	QTY
05-EL-46R6		<i>/-- Rear Load Lights: (2) LED-24, Whelen 900</i>	1
06-EL-18RE		<i>/-- Activate: Rear Flood Switch, Reverse and Lead RA Door</i>	1
		<b>HEAT AND A/C</b>	
05-HA-2005		<i>/-- Patient Ventilation System:4 inch Power Intake, 4 inch Power Exhaust STD</i>	1
05-HB-0150		HVAC System; Pro-Air Ducted Vertical E450 std Mounted Behind the Attendant Seat Base	1
05-HA-1099		<i>/-- AC Evaporator Location: Behind Attendant Seat on the floor</i>	1
05-HA-1301		<i>/-- A/C Condenser: OEM</i>	1
05-HA-1403		<i>/-- AC Hoses: Pre-charged, GoodYear Galaxy</i>	1
05-HA-1404		<i>/-- Heater Hoses: EPDM - Nomex Rubber (per Ford QVM)</i>	1
05-HA-14A0		<i>/-- Side Plenum Grille, Return Air: Stamped Powder Coated Steel</i>	1
05-HA-14B1		<i>/-- Filter, Washable Carbon Pre-Filter</i>	1
05-HA-14C0		<i>/-- AC COMPRESSOR: Tee into OEM</i>	1
05-HA-15A0		<i>/-- Ducted AC Delivery: insulated &amp; foil wrapped, 10 registers</i>	1
05-HA-2005		<i>/-- Patient Ventilation System:4 inch Power Intake, 4 inch Power Exhaust STD</i>	1
05-HB-14PC		<i>/-- AC Evaporator: Pro-Air (AC/Heat unit) w/ dual fans - STD vertical 941</i>	1
05-HA-1404		<i>/-- Heater Hoses: EPDM - Nomex Rubber (per Ford QVM)</i>	1
05-HA-14B5		<i>/-- FILTER: Washable Carbon Pre-Filter</i>	1
10-HA-02ST		<i>/-- AC Control: Heat or AC and Fan Speed selector switches</i>	1
ZZ-ZZ-ZZZZ		<i>/--</i>	1
05-HZ-ZZZZ		<i>/--</i>	1
		<b>CEILING PANELS: ACM Gloss White</b>	
05-IL-0261		<i>/-- Dome Lts, LED K-EDGE (4) Streetside, (4) Curbside std</i>	1
ZZ-ZZ-ZZZZ		<i>/--</i>	1
09-MH-08A1		<i>/-- IV Hook No 1: Hook 07 w/ Velcro bag stabilizer - STD</i>	1
29-MH-1000		<i>/-- LOCATION: Over head/chest area, primary patient on COT</i>	1
09-MH-08A2		<i>/-- IV Hook No 2: Hook 07 w/ Velcro bag stabilizer - STD</i>	1
09-MH-08P2		<i>/-- LOCATION: OH /chest area, secondary patient on S/B</i>	1
ZZ-ZZ-ZZZZ		<i>/--</i>	1
09-MH-2AC5		<i>/-- Recessed C/S Grab Rail, ceiling: 1.25 Dia..... 3 pt, 72in, Gray Anti microbial Grab Rail will be recessed in a ABS pan.</i>	1
09-MH-2ASS		<i>/-- Streetside Grab Rail: None</i>	1
		<b>Insulation PKG: Body Std.</b>	
05-IN-1STD		<i>/-- Insulation: Circumferential PKG, Single Layer Reflective w/ Air cell core</i>	1
05-IN-3STE		<i>/-- Insulation: Entry Door, Reflective w/ Air cell core</i>	1
05-IN-4ST9		<i>/-- Insulation Sound Deadening: Generation 9 Floor</i>	1
05-LB-6100		<i>/-- Light Bar Alternative, (4) Across Front, 92" or wider</i>	1
05-LB-6222		<i>/-- Front of Module SLED System - 92" and wider (4)</i>	1
05-LB-6895		<i>/-- Flasher for LED front of module</i>	1
05-PH-LS0F		<i>/-- Flanges: (4) 900-Chrome Flanges for lights above</i>	1
05-PL-LV12		<i>/-- Light: Whelen 900, Super RED LED/CLEAR LENS,</i>	4
		<b>Non-Programmable IATS</b>	
ZZ-ZZ-ZZZZ		<i>/--</i>	1
05-LB-6900		<i>/-- Alternative Lightbar Switching, Prim/Sec</i>	1
05-SY-LTLE		<b>WHELEN LED WARNING LIGHT SYSTEM - E-series LTD</b>	1
05-FS-0708		<i>/-- Flasher; Electronic LED FM3-01</i>	1
05-FS-10P5		<i>/-- Flash Pattern: KKK-A-1822</i>	1
05-FS-1160		<i>/-- FM3-01 Flash pattern Alternate Flash</i>	1
06-SW-PS01		<i>/-- Warning Light SWITCH: center console, Primary / Secondary</i>	1
ZZ-ZZ-ZZZZ		<i>/--</i>	1
05-PH-LT06		<i>/-- (2) Grille Lights: Whelen TIRLIN3, LED, Chrome Hsg</i>	1
05-FS-1100		<i>/-- Program #25 - Steady Burn, Flash thru Flasher</i>	1
05-PH-LT0A		<i>/-- Lights: (2) Whelen TIRLIN3, RED LED, Chrome Hsg</i>	1

PART NO	S	DESCRIPTION	QTY
05-PL-LU20		-- (2) Front Intersection Lts: Whelen 700, LED (Super LED):	1
05-PH-LT09		-- Flanges: (2) 700-Chrome Flange for lights above	1
05-PL-LX52		-- Lights: (2) Whelen 700, Super RED LED/CLEAR LENS, Non-Programmable ILOS	1
ZZ-ZZ-ZZZZ		--	1
05-PL-LU30		-- (1) Center Front Warning Light : Whelen 900 (Super LED)	1
05-PH-LS0H		-- Flange: (1) 900-Chrome Flanges for light above	1
05-PL-LXF0		-- Light: Whelen 900, Super WHITE LED/CLEAR LENS, Non-Programmable ILOS	1
ZZ-ZZ-ZZZZ		--	1
05-PL-LU40		-- (2) Front Warning Lts: Whelen 900, (Super LED)	1
05-PH-LS0A		-- Flanges: (2) 900-Chrome Flanges for lights above	1
05-PL-LXF2		-- Light: Whelen 900, Super RED LED/CLEAR LENS, Non-Programmable ILOS	2
ZZ-ZZ-ZZZZ		--	1
05-PL-LU50		-- (4) Side Warning Lts: Whelen 900, (Super LED)	1
05-PH-LS0F		-- Flanges: (4) 900-Chrome Flanges for lights above	1
05-PL-LXF2		-- Light: Whelen 900, Super RED LED/CLEAR LENS, Non-Programmable ILOS	4
ZZ-ZZ-ZZZZ		--	1
05-PL-LU54		-- Rear Intersection Lights, : NONE	1
ZZ-ZZ-ZZZZ		--	1
05-PL-LU60		-- (2) Rear Warning Lts: Whelen 900, (Super LED) ilos	1
05-PH-LS0A		-- Flanges: (2) 900-Chrome Flanges for lights above	1
05-PH-LT6A		-- Location: REAR, (1) in EACH Upper outer corner.	1
05-PL-LXF2		-- Light: Whelen 900, Super RED LED/CLEAR LENS, Non-Programmable ILOS	2
ZZ-ZZ-ZZZZ		--	1
05-PL-LU61		-- (2) Rear Warning Lts: Whelen 900, (Super LED), IATS	1
05-PH-LS0A		-- Flanges: (2) 900-Chrome Flanges for lights above	1
05-PH-LT6B		-- Location: REAR, (1) aligned w/ EACH upper window in RA doors.	1
05-PL-LV12		-- Light: Whelen 900, Super RED LED/CLEAR LENS, Non-Programmable IATS	2
ZZ-ZZ-ZZZZ		--	1
05-PL-LU70		-- (1) Rear Center Warning Lt: Whelen 600, (Super LED) ILOS	1
05-PH-LS0K		-- Flange: (1) 600-Chrome Flanges for lights above	1
05-PL-LXH6		-- Light: Whelen 600, Super AMBER LED/CLEAR LENS, Non-Program ILOS	1
ZZ-ZZ-ZZZZ		--	1
ZZ-ZZ-ZZZY		--	1
ZZ-ZZ-ZZZZ		--	1
<b>ELECTRICAL - CELL 3</b>			
06-00-0004		-- Customer Supplied Part(s) : NONE ITEMS MUST BE NEW, No USED items accepted. Required under GSA-K-1822 and CAAS GVS.	1
ZZ-ZZ-ZZZZ		--	1
11-ZZ-090D		-- CAAS GVS 2.0 Exception C.8.5.5 Lack of Automatic Anti-Theft device for Idling By declining to select an appropriate anti-theft device for this chassis, The Agency is non-compliant to CAAS GVS 3.0 for the likely event of an Automatic Anti-Theft device required idling of the chassis while unattended.	1
ZZ-ZZ-ZZZZ		--	1
06-AM-SAH5		-- AEV Trauma Hawk Telematics System - T1,3 AEV RMR-LX1 etc Ford Vehicles	1
AEV remote vehicle monitoring Gen 3 system Telematics (Most AEV Electrical systems) Antenna to be mounted on chassis cab roof,			

PART NO	S	DESCRIPTION	QTY
		12 months of subscription software licence included in purchase. one speaker in chassis cab SPEA-SH80, in console, Driver ID Fob reader installed on front console Includes (5) ID-FOBS for driver identification (ship with vehicle) , WIRE TIE these fobs to the Acetech system for the customer to remove at comissioning of the vehicle.	
06-AM-SAL1		-- Location: Behind Passenger seat	1
06-RR-0707		-- (1) Speaker: Connect to AEV Traumahawk Telematics in ACTION AREA	1
06-BA-3F21		Batteries: 2 - Battery System - E-series Gas Only	1
06-BA-3FD2		-- Battery Make: (2) Motorcraft-OEM	1
06-BA-3FM1		-- Batt Loc: (T3) (1) Underhood, Remainder Batt M-8	1
06-BA-Q630		-- Battery Switch: Cole Hersee 2484-16 Paddle, T3 Driver seat base LOCATION: Side of drivers' seat base.	1
06-BA-3FW4		-- Batteries Wired: Parallel for higher amperage	1
ZZ-ZZ-ZZZZ		--	1
06-EC-0501		Door Locks, MODULE: Manual Key Operated	1
06-EC-3013		-- 3rd Brake Light with back-up camera VCAHD140LB, White,Mirror Monitor CHECK THAT NO OTHER CAMERAS ARE SELECTED	1
06-EC-3507		Circuit Board: RMR Rail System, W/ LED Diagram - E Series	1
06-EC-3570		-- Master Switch: Front Only	1
06-EC-CB03		-- Circuit Protection, 12V: Blade Breaker - Manual-reset	1
06-RR-23F1		-- Ind Light Flasher: Thru 14S Flasher Unit	1
06-RR-F301		-- CONSOLE, Engine Cover: 2-level Roto-molded ABS E series -	1
06-RR-2310		-- SWITCH PANEL: Front and Rear Standard - LED Rocker E- Series	1
06-MC-0810		-- Smart Volt Meter: (1) Kinequip 8.0 thru 16.0 Volts, Digital w Low voltage buzze	1
ZZ-ZZ-ZZZY		--	1
06-RR-23A1		-- Engraved LOGO: AEV TraumaHawk	1
06-RR-2311		-- Indicator Light: Halogen AMBER "Compt Open" light	1
06-RR-2312		-- Flashing light: Activate w/ ANY compartment door switch.	1
06-RR-2313		-- Indicator Light: halogen GREEN "AMB PWR" light	1
06-RR-2314		-- Steady burn light: Activate with Conversion power switch	1
06-RR-2315		-- Indicator Light: Halogen RED "Door Ajar" light	1
06-RR-2316		-- Flashing light: Activate w/ ANY Mod entry door switch.	1
06-RR-23J3		-- Door/Compartment Ajar Buzzer: None	1
06-RR-23L0		-- Illumination strip LED for Front and rear switch panels 12v	1
06-RR-F311		-- Fasteners: Black finish screws into engine cover	1
07-ZZ-ZZZZ		--	1
06-EC-4300		Back-up Alarm: Standard 102DB	1
06-EC-43C0		-- Cut Off Switch: NONE	1
06-EC-GR01		Ground Straps, Module to Frame: (Qty 4) Braided	1
06-IA-0001		Converter , 125V to 12V: NONE	1
06-IG-0200		<b>Inverter System: Ford Gas Engine Package (Only) Mod</b>	1
06-IG-0250		-- Inverter : Vanner LIFESINE 1100 Pure Sine Wave, w 55watt 3 stage charger	1
06-EC-03AS		-- Portable Equip Charging Circuits: Included in Inverter	1
06-EC-03AA		-- PREWIRE LOCATION: (1)Cab Console, (1) Behind A/A	1
06-EC-03C9		-- Portable Equip Pwr Source: Ignition and/or Shoreline	1
06-IG-03A0		-- Battery Charger/Conditioner: 55A - Built into Inverter	1
06-IG-0003		-- Built-in Battery Charger: Enable - Wire to Batteries	1
06-IG-04L0		-- Inverter Location: M-2 (LFM) Compartment	1
06-IG-04M0		-- On Floor near wall #1	1
06-IG-04C0		-- Lexan Cover: Over Inverter	1



PART NO	S	DESCRIPTION	QTY
ZZ-ZZ-ZZZZ	--	<b>COMMUNICATION RADIO(S) RELATED RADIO POWER</b>	1
06-EC-03A0	--	Radio Power No 1: 30A, Pos and Neg, 10 awg Wires	1
06-EC-03B0	--	Radio Power Source: Battery Switch Hot	1
06-EC-03G0	--	LOCATION: Behind Passenger's Seat	1
06-EC-03A2	--	Radio Power No 2: 30A, Pos and Neg, 10 awg Wires	1
06-EC-03B0	--	Radio Power Source: Battery Switch Hot	1
06-EC-03E0	--	LOCATION: Behind Action Area Board	1
<b>ANTENNA LEADS</b>			
06-RR-0100	--	Coaxial Cable, No 1: Type RG-58U, No connectors	1
06-RR-0101	--	ORINATION POINT: Roof Port No 1	1
Roof Port No 1 is lined up with the edge of the curbside entry door, and centered side to side as possible			
06-RR-01P0	--	Port Plate: None - Access thru center upholstery panel	1
06-RR-01T1	--	TERMINATION POINT: Behind Passenger's seat w/ 36" Tail	1
06-RR-1809	--	Patient Area Radio : None	1
06-SO-0000	125V SHORE LINE AND OUTLETS		1
06-SO-0105	--	<b>Shore Line Inlet: 20A T blade w/ Ground - ILOS</b> plug-5374BK ship loose	1
06-SO-00L1	--	<b>Inlet location: Aft of Left Front compartment</b>	1
06-SO-1400	--	**125 Volt OUTLETS**	1
06-SO-1401	--	125 VAC Outlet, No 1: 15A, Hospital Grade, IVORY	1
All 125 VAC outlets shall be back lighted when power is applied to the outlet.			
06-SO-14L1	--	LOCATION: Action Area, standard location	1
06-SO-14O2	--	Outlet mounting ORIENTATION: Vertical	1
ZZ-ZZ-ZZZZ	--		1
06-SO-14O2	--	125 VAC Outlet, No 2: 15A, Hospital Grade, IVORY	1
06-SO-14L3	--	LOCATION: RF ALS, (See Drawing)	1
06-SO-14O2	--	Outlet mounting ORIENTATION: Vertical	1
ZZ-ZZ-ZZZZ	--		1
06-SO-1100	**INTERIOR 12 Volt OUTLETS**		1
06-SO-1101	--	12V Outlet, No 1: Power Point Double Outlet- Wire thru Med Isolator	1
06-SO-11L1	--	LOCATION: Action Area, standard location	1
06-SO-14O2	--	Outlet mounting ORIENTATION: Vertical	1
06-SO-1910	--	Power Source: Medical Isolator , Batt Sw Hot	1
ZZ-ZZ-ZZZZ	--		1
06-SS-0600	Siren: Whelen, 295SLSA1, E-Series		1
06-SS-SA19	--	Speaker, Grille, dual, (SA315EKT-Pair) E-Series	1
06-SS-SW01	--	Siren / OEM Horn Switch: In Cab Console	1
06-SS-SW04	--	microphone clip not installed Tie to Siren Microphone cord.	1
<b>CABINET SHOP - Modular</b>			
ZZ-ZZ-ZZZZ	--		1
07-00-0001	ALL DIMENSIONS ON ORDER WILL HAVE A VARIABLE OF + OR - 1/4" Unless specified as a minimum dimension.		1
ZZ-ZZ-ZZZZ	--		1
<b>Cabinet Configuration</b>			
07-00-164E	CABINET CONSTRUCTION, GENERAL, 164 X 95 E-SERIES		1
ZZ-ZZ-ZZZZ	--		1
07-00-BH01	BULKHEAD PANELS: See Station 5 See Station 5 portion of shop order to find DOOR info.		1

PART NO	S	DESCRIPTION	QTY
ZZ-ZZ-ZZZZ	--		1
07-00-MC03		<b>Mica Color: Gloss White D354F-01</b>	1
07-00-N002	--	<b>All Cabinet interiors Standard Pre-laminated &gt; WHITE</b>	1
ZZ-ZZ-ZZZZ	--		1
07-00-PC0N		<b>Polycarbonate Type/Color: Lexan - CLEAR Secure Latch</b>	1
07-02-0074	--	<b>Att Seat: EVS, Comfort 1780 Black, Vacuum Form, Per4Max Black belt</b>	1
07-SE-0209	--	<b>BASE: EVS Seats, Metal, Mica Covered Base, Match Unit Interior</b>	1
07-DR-WD01	--	<b>Door, Single Solid Flush Fitted</b>	1
07-CA-2100	--	<b>TRIM: U-shaped Door, J-trim opening</b>	1
07-DR-OR02	--	<b>Hinge Orientation: BOTTOM</b>	1
07-HW-HIN1	--	<b>Hinge: 1 1/2" Stainless Steel Piano Hinge</b>	1
07-HW-SO01	--	<b>Lever Latch: Non-locking - Black Finish -8 lb rated</b>	1
11-SE-04A0	--	<b>Attendant Seat, Armrest: None</b>	1
ZZ-ZZ-ZZZZ	--		1
07-AC-6401		AC CABINET: Evaporator, Std Location Behind Att Seat Faces Aisle	1
07-ZZ-ZZZZ	--		1
07-BH-6401		Bulkhead Cabinet "J": Standard	1
07-BH-6402	--	Cabinet "J": Over Att Seat	1
07-DR-LX24	--	Door: Single Flip Up 3/8" Lexan	1
07-DR-LZ20	--	Hinges: Reel Torque	1
07-HW-SO01	--	Lever Latch: Non-locking - Black Finish -8 lb rated	1
07-ZZ-ZZZZ	--		1
07-ZZ-ZZZZ	--		1
07-ZZ-ZZZZ	--		1
07-ZZ-ZZZZ	--		1
07-CA-04B0		CURBSIDE REAR STORAGE CABINET: NONE	1
07-ZZ-ZZZZ	--		1
07-LF-6401		LF Cabinet, Behind Att Seat: Cabinet "H"/(Elec Cab)	1
07-CA-VEN7	--	Plastic Vent: (2) Total, 1 column x 8 row, Vent 01	1
07-DR-WD0E	--	Door, Single Solid Flush Fitted Electrical Area	1
07-CA-2100	--	TRIM: U-shaped Door, J-trim opening	1
07-DR-OR04	--	Hinge Orientation: RIGHT	1
07-HW-HIN1	--	Hinge: 1 1/2" Stainless Steel Piano Hinge	1
07-HW-SO04	--	Lever Latch: Non-locking - Black Finish Non Storage areas, no rating applied	1
07-ZZ-ZZZZ	--		1
07-RF-6401		RF ALS Cabinet: Standard	1
07-RF-I164	--	Cabinet I-1: Standard	1
07-DR-LX24	--	Door: Single Flip Up 3/8" Lexan	1
07-DR-LZ20	--	Hinges: Reel Torque	1
07-HW-SO01	--	Lever Latch: Non-locking - Black Finish -8 lb rated	1
07-ZZ-ZZZZ	--		1
07-RF-I264	--	Cabinet I-2: Standard	1
07-DR-WS03	--	Doors: Dual Flush Fitted 6" Secure latch Top and Magnets at Bottom Secure latches installed at top of each door, Magnets at the bottom of the door.	1
07-CA-21A0	--	TRIM: U-shaped Door, J-trim opening, DBL DRS	1
07-DR-OR05	--	Hinge Orientation: (1) RIGHT and (1) LEFT	1
07-HW-HIN1	--	Hinge: 1 1/2" Stainless Steel Piano Hinge	2
11-X0-0045	--	Stowage rating label Secure Latch 6" Single Handle on Door 20 pounds applied	1
07-RA-IOA1	--	Outside Access: Thru M-7 (RF) Compartment door.	1
07-RF-0001	--	Interior MICA Color: White cabinet liner	1
07-TS-1200	--	Shelf Track: Small alum Unistrut type	1
07-CA-0600	--	(1) Shelf: Adjustable with Alum Trim	1
ZZ-ZZ-ZZZZ	--		1

PART NO	S	DESCRIPTION	QTY
07-RF-I268		-- Cabinet I-3: Standard 15" Interior Height.	1
07-DR-WD25		-- Door, Single Solid, Flush - Drug Locker	1
07-CA-2100		-- TRIM: U-shaped Door, J-trim opening	1
07-DR-OR02		-- Hinge Orientation: BOTTOM	1
07-HW-HIN1		-- Hinge: 1 1/2" Stainless Steel Piano Hinge	1
07-HW-SO02		-- Lever Latch: Locking - Black Finish 8 lb rated	1
07-RA-IOA1		-- Outside Access: Thru M-7 (RF) Compartment door.	1
07-RF-0001		-- Interior MICA Color: White cabinet liner	1
07-RR-0064		Right Rear Cabinet: Cover over M-5 Compartment	1
07-ZZ-ZZZZ		--	1
07-SA-0000			1
07-SB-6401		SQUAD BENCH: Standard 164-172	1
07-SB-0001		-- See Upholstery Section for Post and Wheel Cup info	1
07-SB-1001		-- Storage Under Lid - Configure to M-6 Compartment Size	1
07-SB-LID2		-- Squad Bench Lids: Split - 2-section	1
07-SB-LH00		-- Hinge, Squad Bench Lid(s): Butt Style Hinges	1
07-SB-LH03		-- Lid Checks: Gas shock, Dual Action	2
07-SB-LH07		-- Latch, Squad Bench Lid: Slam Action Paddle, W keeper -80 lb rated	2
07-TR-SB01		-- Edge Trim, Lids: Band w/ Laminate and J-Trim Protection	1
ZZ-ZZ-ZZZZ		--	1
08-MH-1400		-- Restraint Net, Black, 7 point detachable, at head of S/B, Mod Seven (7) NET Attachment Points: Black in color. NETS-MOD2	1
08-ZZ-ZZZZ		--	1
07-TC-6401		TOP CABINETS, - Standard	1
07-TC-A644		-- Cabinet A: Standard	1
07-DR-LX24		-- Door: Single Flip Up 3/8" Lexan	1
07-DR-LZ20		-- Hinges: Reel Torque	1
07-HW-SO01		-- Lever Latch: Non-locking - Black Finish -8 lb rated	1
07-ZZ-ZZZZ		--	1
07-TC-B641		-- Cabinet B: Ergonomically angled toward the CPR seat	1
07-CB-DR30		-- Doors; Cabinet B Secure Latch Sliding Window	1
11-X0-0014		-- Stowage rating label - Secure Latch Sliding Window 40 pounds applied each	1
07-ZZ-ZZZZ		--	1
07-ZZ-ZZZZ		--	1
07-WC-0000			1
07-WC-6401		WALL CABINET: CPR Seat w/Telemetry Type 3	1
07-WC-AA01		-- Action Area: Standard	1
07-WC-AA02		-- A/A Tray: Color Keyed Mica with ABS BioWaste	1
07-SB-1005		-- WASTE CONTAINER: 6 Quart std -CANO-04G	1
07-SB-1008		-- SHARPS CONTAINER: 2-Gallon Sharps-A-Gator (CONT-02)	1
07-WC-AABD		-- Action Area Board: Black Grip See Station No 6 for content	1
07-ZZ-ZZZZ		--	1
07-WC-C641		-- Cabinet C: Standard	1
07-CB-DR34		-- Doors; Cabinet C Secure Latch Sliding Window	1
11-X0-0014		-- Stowage rating label - Secure Latch Sliding Window 40 pounds applied each	1
07-RF-0009		<b> -- Inside Access / Outside Access</b>	1
07-ZZ-ZZZZ		--	1
07-WC-D641		-- Cabinet D: Ergonomically Angled Cabinet Over Tele. Area	1
07-CB-DR36		-- Doors; Cabinet D Secure Latch Sliding Window	1

PART NO	S	DESCRIPTION	QTY
11-X0-0014		-- Stowage rating label - Secure Latch Sliding Window 40 pounds applied	1
		each	
07-ZZ-ZZZZ		--	1
<del>07-WC-E003</del>		<del> -- Cabinet E: DELETE</del>	<del>1</del>
<del>07-ZZ-ZZZZ</del>		<del> --</del>	<del>1</del>
07-WC-F641		-- Cabinet F: Standard	1
07-CB-DR46		-- Doors; Cabinet F Secure Latch Sliding Window	1
11-X0-0014		-- Stowage rating label - Secure Latch Sliding Window 40 pounds applied	1
		each	
07-ZZ-ZZZZ		--	1
07-WC-SS01		-- CPR Side Seat: 24" inch - Single Position - Standard	1
07-WC-BR01		-- Back Rest: Fixed to Back Wall of CPR Seat w/clips	1
ZZ-ZZ-ZZZZ		--	1
07-WC-TA01		-- Telemetry Area: with armrest pad	1
07-WC-TC03		-- Telemetry Area: Mica Finish, color keyed to interior	1
		With 3/4" Lip	
ZZ-ZZ-ZZZZ		--	1
07-WC-O101		-- Cabinet O1: Standard	1
07-CB-DRLY		-- Door: Single Overlay Lexan Hinged Right	1
07-HW-SO11		-- Round Pull Latch: Non-locking - Chrome Finish ILOS -10 lb rated	1
07-HW-SO01		-- Lever Latch: Non-locking - Black Finish -8 lb rated	1
ZZ-ZZ-ZZZZ		--	1
08-SE-1702		-- P4 - 4-Point PER4MAX Restraint System - W/CPR	1
08-SE-1721		-- (2) on Squad Bench, (1) CPR Side Seat Per4Max above bench black Belts	1
08-SE-SB70		-- S/B: (3) Sec patient restraints - 9" Sleeves Face of Bench	1
08-SE-SB76		-- S/B: (3) Sec patient restraints - 5" Sleeves By Hinge	1
00-20-0072		-- Per4Max Four-Point Seatbelts: Accept and Install Full Feature	1
		<b>AEV Rolltek AIRBAG System Options</b>	
ZZ-ZZ-ZZZZ		--	1
07-ZZ-ZZZZ		--	1
		<b>CABINET SET - CELL 4 - MOD</b>	
08-00-00PW		Sub Floor, 3/4" Plywood, Standard	1
<del>08-00-FL3A</del>		<del><b>Flooring: Loncoin II Flecks- #150, Onyx (Black)</b></del>	<del>1</del>
<del>08-00-FL01</del>		<del><b> -- Flooring Main Edge: 3" Recessed (1/2" deep) roll-up</b></del>	<del>1</del>
<del>08-AS-0001</del>		<del><b> -- Rear Threshold, Stainless, 6" Wide x Full Width at rear doors</b></del>	<del>1</del>
		Install safety yellow with diagonal stripes nonskid tape over threshold.	
<del>08-AS-0006</del>		<del><b> -- C/S Stepwell Threshold, Polished Diamond Plate</b></del>	<del>1</del>
<del>ZZ-ZZ-ZZZZ</del>		<del> --</del>	<del>1</del>
<del>08-ZZ-ZZZZ</del>		<del> --</del>	<del>1</del>
08-CS-0001		COT MOUNT HARDWARE: (Full Size Mod)	1
<del>08-CS-CMTD</del>		<del><b> -- Cot Mount: To Be Determined when sold</b></del>	<del>1</del>
		Mount Position: Center	
08-OS-04ST		OXYGEN / AIR / VACUUM System:	1
08-OS-0401		-- Oxygen Outlet No 1: Amico Console - Ohmeda/Ohio Diamond Style	1
08-OS-040A		-- LOCATION: Action Area	1
08-OS-0402		-- Oxygen Outlet No 2: Amico Console - Ohmeda/Ohio Diamond Style	1
08-OS-040A		-- LOCATION: Action Area	1
<del>08-OS-0403</del>		<del><b> -- Oxygen Outlet No 3: Amico Console - Ohmeda/Ohio Diamond Style</b></del>	<del>1</del>
<del>08-OS-040D</del>		<del><b> -- LOCATION: Curbside Wall, over the head of the S/B</b></del>	<del>1</del>
ZZ-ZZ-ZZZZ		--	1
08-OS-1331		-- Rack No 1: Adjustable AEV O2 Rack Green with 4 Ratchet Straps M/H	1
		Fits cylinders 7" diameter or more.	

PART NO	S	DESCRIPTION	QTY
08-OS-11G1		-- Cylinder Type: OXYGEN - Green Colored Hose Regulator connection Nut: 9/16" RH thread.	1
08-OS-1301		-- Rack Location: Left Front, wall #2 near wall #3	1
08-OS-132M		-- Set up For M cylinder	1
08-OS-1710		-- Regulator, Oxygen, Fixed output @ 50 psi +/-5 , CGA 540, Installed STD Installed on O2 line for pressure test, Tagged with Inspector signature/Date	1
08-OS-1902		-- Regulator Wrench: Cast aluminum, OXYGEN w/ cable lanyard	1
ZZ-ZZ-ZZZZ		--	1
08-OS-35ST		-- Vacuum System: SSCOR regulator/gauge panel in A/A	1
08-OS-3501		-- Collection Canister w Clip: Bemis, 1200 CC at Action Area	1
08-OS-3502		-- VAC Plumbing: Direct from panel to canister - NO Outlet	1
08-OS-3503		-- Vacuum Pump: 49 State	1
08-OS-35L4		-- Location: M-2 Compartment	1
ZZ-ZZ-ZZZZ		--	1
<b>TRIM / DOOR ASSEMBLY - CELL 5</b>			
09-00-002S		-- Interior window and aluminum trim with standard satin finish- std	1
09-00-0001			1
09-00-0002		*****DOOR DEPARTMENT - Full Mod*****	1
02-BT-C853		-- Handles, Ext: Tri-mark 030-1875, Free Float, Polished CNNC finish	1
02-BT-C85A		-- Interior Release: All Entry Doors, with bezel Emergency Access	1
09-MH-2530		-- Grab Rail, (1), 18" Gray Antimicrobial Rear Entry Assist std. Located : Module interior at the rear entry, mounted to the M5 compartment filler. Rail is to be through bolted into M5.	1
09-MH-2702		-- Grab Rail, C/S wall, Various types C/S Entry, NONE	1
ZZ-ZZ-ZZZZ		--	1
09-B1-ED00		Entry Door Panels, Windows and Hardware	1
08-MH-0010		-- Interior Grab Handle Color: Gray Antimicrobial	1
08-MH-03B3		-- Grab Handle, CS Entry: 1 1/4" Dia..... S/S, 2-pt 18"L, Gray Antimicrobial	1
08-MH-03D3		-- Grab Handles, Rear Access: (2) 12"L X 1 1/4" Dia..... S/S, 2-pt, Gray Antimicrob	1
09-AS-2400		-- Door Panels: Diamond Plate / Upholstery / Diamond Plate	1
09-AS-2510		-- Curbside Lower Door Panel: Diamond Plate	1
09-WI-02A0		-- UPPER Windows: RA Doors, Fixed Tinted Glass 17.3"W x 19.3"H WIND-H0161	1
09-WI-0600		-- UPPER Window: CS Access, Fixed Glass, std tint WIND-H0161	1
09-DR-WT03		Walk through Door: Slide behind drivers seat fixed window	1
07-ZZ-ZZZZ		--	1
<b>ELECTRICAL Point to Point - CELL 6</b>			
10-IL-02ST		Action Area Light: 12V, LED, Surface Mount	1
10-IL-02L7		-- Light Location: Action Area	1
<b>UPHOLSTERY - CELL 7</b>			
11-00-UB95		<b>Upholstery Color: Black ( Black ) UPHO-6905</b> UPHO-6905	1
11-00-UC11		<b> -- Center Trough Upholstery Color: Color Key to Rest of Truck</b>	1
ZZ-ZZ-ZZZZ		--	1
11-00-UT05		Uph Joint Type: Vacuum Formed - Seamless	1
11-05-0015		Cab Extension Dove Gray Vinyl Standard	1
11-SB-0005		Squad Bench seat cushion cut-outs: None	1

PART NO	S	DESCRIPTION	QTY
11-SB-0003		-- Post And Wheel Cups: NONE	1
11-SE-CSPD		Head Protection: Pad over CS Entry Door	1
11-SE-REPD		Head Protection: 2" Pad over Rear Access Doors, Full Width	1
<b>PAINT - STRIPES - DECALS</b>			
12-PT-UNCT		-- Undercoating : Per QVM Guidelines, STD	1
12-DC-0001		Reflective Tape: White Reflective On Painted edges of Exterior Door Frame	1
12-DC-GA10		Compartment Finish: Diamond Plate Standard	1
12-PT-0100		Primary (Over All) Color: White (YZ)	1
12-DC-0002		-- Flip Step Reflective/Prismatic Tape: Red/White/R/W/R/W/R	1
12-PT-0112		-- Tape Stripe: NONE (KKK-F Deviation)	1
11-YZ-0962		-- Non-Compliant to KKK-F 3.16.2 ; Exterior Safety stripe to be Orange	1
12-PT-0600		-- Paint Belt: NONE	1
12-PT-1000		-- Pin Stripe: NONE	1
12-ZZ-ZZZZ		--	1
12-PT-RF01		-- Roof Paint: Color and finish quality to be GLOSSY	1
ZZ-ZZ-ZZZZ		--	1
12-PT-2000		Lettering: NONE	1
12-ZZ-ZZZZ		--	1
12-PT-DRIP		Drip Rails: Bright Aluminum, De-burred and rounded corners Include a drip rail over the C/S Entry Door.	1
<b>DETAIL - SHIP LOOSE ITEMS</b>			
12-PT-DRIZ		-- Drip Rails: Detail-Refer to Paint Section for Drip Rail Information Include a drip rail over the C/S Entry Door.	1
13-00-0200		-- *Check front of W/O under chassis section for Add' items*	1
ZZ-ZZ-ZZZZ		--	1
13-10-XM00		-- Owner's Manual USB Flash Drive ship loose	1
13-10-XMA0		-- Printed Owner's Manual Not Required	1
13-00-0001			1
13-GL-0000		Glove Holder, Ship Loose: NONE	1
ZZ-ZZ-ZZZZ		--	1
13-KK-KDEC		Decals: KKK / DOT Pkg, Blue/White reflective - Ship Loose	1
13-RF-STAS		-- Decals: 32" Star of Life - Ship Loose	1
ZZ-ZZ-ZZZZ		--	1
13-KK-NSSB		Decals: NO SMOKING & SEATBELT, installed, cab & pt. area.	1
ZZ-ZZ-ZZZZ		--	1
13-KL-0010		AEV Logos: Installed on unit per AEV standard locations	1
13-MH-05ST		Fire Extinguisher, 5 pound, shipped loose, Std	1
11-YZ-0932		-- Exception to 3.15.2 Required Two fire extinguishers installed by FSAM Fire extinguishers were not installed with one in the driver's cab, one in the patient compartment at the time of departure from the final stage Ambulance Manufacturer. The customer/FSAM has shipped them loose for the dealer to complete the final install.	1
11-ZZ-0932		-- Exception to C.16.1 1 Required Two fire extinguishers installed by FSAM Fire extinguishers were not installed iwth one in the driver's cab, one in the patient compartment at the time of departure from the final stage Ambulance Manufacturer.	1
13-MH-10A0		Reflector Pkg: Body - 2ea, Side Fr Amber, Side Rear Red, Rear Red	1
ZZ-ZZ-ZZZZ		--	1
13-MR-0000		Convex Mirrors: None	1
13-SB-0003		Post And Wheel Cups: NONE	1
13-SP-TIRE		Spare Tire: Refer To Chassis Section to See if it gets one.	1
34-XX-0001		-- Primary Cot: NONE included	1
ZZ-ZZ-ZZZZ		--	1
34-XX-0002		-- Secondary Stretcher: NONE included	1

PART NO	S	DESCRIPTION	QTY
ZZ-ZZ-ZZZZ		--	1
34-XX-5000		Indemnification Statement The purchaser agrees to defend, indemnify and hold REV harmless from any claims, costs (including actual attorneys' fees), damages and liabilities caused in whole or in part by any alteration or modification of, or changes or additions to the Purchased Products OR use of product for purposes it was not designed or intended for.	1
<b>GENERAL CONVERSION</b>			
36-AA-0001		WORK ORDER STATUS:	1
00-90-0301		-- For Confirmation	1
36-CO-0001		-- CHANGE ORDER POLICY	1
36-CO-0010		-- After Confirmation, Prior to Engineering Change Fee is \$100 Per Item, Plus Option Cost	1
36-CO-0030		-- After Confirmation, After Production Start Change Fee is \$200 Per Item, Plus 200% Option Cost Additional labor charges above option costs may apply to accomodate the change at \$200 per hour. Special order or non-stocking parts that are purchased for any ordered option that is subsequently deleted will be charged for and shipped loose. >> Changes after production starts are the most disruptive.	1
36-CO-0035		-- Change Order Recieved at Delivery ; \$300 charge per item, plus three times the standard option cost AND Any additional labor to accomodate the change at \$200 per hour, Effective 01/28/2022	1
ZZ-ZZ-ZZZZ		--	1
36-EO-0001		-- ***END OF ORDER***	1